Cougar EVO

The efficient, small-footprint inspection system for SMT, semiconductors and labs.



c•met yxlon


Comet Yxlon this is who we are. Comet Yxlon designs and manufactures high-end X-ray and CT system solutions for industrial environments – based on customer-centric product development. We're proud to be part of Comet, the globally leading Swiss technology company with a focus on plasma control and X-ray technology. Led by experience. Driven by curiosity.

Deeper insights.

Looking beyond the surface is our core competency at Comet Yxlon – but not only in a technical way.

Zooming in on your industry, applications and business challenges allows us to develop innovative and relevant solutions that help you shape future markets.

Faster time to market? Avoiding production downtimes? The perfect image with the highest resolution, as fast and easy as possible? Whatever your goal – let's talk about it!



Automated 2D and laminography inspection for maximum productivity.

Your benefits with the Cougar EVO:

- Reliable, fast and repeatable inspections manually and automatically
- Increased efficiency through automated inspection and softwareassisted image review
- Easy-to-use dynamic image enhancement filters, e.g. eHDR
- Best available laminography
- Dose monitoring for sensitive parts
- Smallest footprint available on the market

2 COMET YXLON COUGAR EVO COMET YXLON COUGAR EVO

Small footprint. Smart capabilities.

Connectivity, self-optimizing processes, automation – Industry 4.0 demands new solutions. Challenge accepted: The Cougar EVO helps increase speed, image quality, and efficiency in the SMT and semiconductor industry as well as in laboratories.

Already Aristotle realized: "The whole is greater than the sum of its parts". With the Cougar EVO it's the combination of innovative visualization software, smart workflows like VoidInspect, and an astounding compactness that makes this system stand out.

Footprint: only one sqm

existing elevators can be used.

Minimum size meets maximum performance: With its compact dimensions, the Cougar EVO is the perfect choice for facilities with space limitations. The weight of the Cougar EVO makes it suitable for many standard building floors. In addition, its size and weight enable a quick and hassle-free transport into the location – in many cases, the

Increase yield

Deeper insights from repeatable scan results keep your production on target.

Improve your efficiency

Faster results due to dedicated inspection workflows boost your productivity.

Enhance your quality

Precise image details reveal process trends.

Smart workflows and visualization


The Cougar EVO responds to the need for improved, automated operation with integrated workflows in the FGUI operating software. Once images are captured, the Comet Yxlon FF CT software automatically performs a fast reconstruction of outstanding quality and, finally, offers brilliant visualization. It has a unique ability to render 3D cinematic images with a preset selection of transfer functions (TF), resulting in the most realistic, vivid visualization.

Large flat-panel detectors

The Cougar's large flat-panel detectors offer an up to 50% larger field of view for a better overview. Manufacturers benefit from faster working processes due to the reduced number of steps in automated processes.

Production line integration with ProLoop

The Cougar EVO supports ProLoop, Comet Yxlon's smart factory solution for the optimization of production processes. It enables direct communication with the inline AOI / AXI inspection systems and thus helps achieve maximum yield performance.



Voiding in BGA balls detected with laminography scan.

4 COMET YXLON COUGAR EVO


Different applications. Same great quality.

SMT inspections: grand performance for small devices

Due to the miniaturization and performance increase of more and more features must fit in an ever-smaller area. Cougar enables accurate, repeatable inspection routines with void compilations, including multi-area voiding. It does not only provide high performance and resolution, but is also equipped with enhancement filters and powerful automation tools.

SMT applications

· · · · · · · · · · · · · · · · · · ·
PCB (BTC, BGA, LGA, QFN/QFP, THT)
IGBT
LED



Computed laminography of PCB, clipping plane

Semiconductor inspections: maximum resolution at minimum voltage


Cougar enables accurate, repeatable inspection routines with void compilations, including multi-area voiding. Its high detail resolution laminography is key for inspecting the internal connections of state-of-the-art advanced packaging IC devices.

Semiconductor applications


Wafers and integrated circuits (die attach connections, 3D IC joints, TSV)

sensors

 $\mathsf{MEMS} \; \mathsf{and} \; \mathsf{MOEMS}$



Overview of BGA and bumps with laminography



3D visualization of a multi-layer board, using the Comet Yxlon FF CT Software.

Laboratory inspections: leading technology for precise analysis

The inspection of electronic components during research and development is highly complex and requires a broad range of features. Computed tomography with the Comet Yxlon Cougar EVO is the technology of choice for detailed analyses of micro components such as those used in batteries, connectors, and medical devices.

Lab applications

Ratteries

Connectors and other electronics components


Medical material

Military and space electronics


Software solutions for accurate, repeatable, fast results.


From image acquisition with the FGUI user interface, to the reconstruction of the volume with FF CT software, to image analysis and evaluation: the Cougar offers a wide range of integrated software features. They help increase the efficiency of manual labor - and save inspection cost per part.





THT with voiding





Voiding with BGA balls

THTInspect DR

THTInspect DR is the semi-automated defect analysis for fill level inspections on THT-based components in 2D. It enables an assisted inspection routine for quantitative analysis, in both sampling and batch testing and works with plated and non-plated pin holes. The evaluation results according to specification are visualized in green and red.

VoidInspect CL and DR

VoidInspect facilitates best-in-class analysis of solder shapes and related cavity defects based on computed laminography (CL) or digital radiography (DR) technology. It is an automated inspection routine for quantitative analysis, with very high accuracy and repeatability, that helps save time and minimize error. It is qualified for the inspection of electronic components like BGA, LGA, BTC and QFN Central Pads, LED, IGBT and DPAK.

2D multi grea void calculation (MAVC)

QFNs and other bottom-terminated devices without overlapping can also be inspected with 2D digital radioscopy. Faulty or missing solder joints and large areas of voiding are reliably detected, and MAVC helps analyze voids in complex soldering designs. With just four parameters to adjust, setup is quick, simple, and costefficient. Precise void analysis of multi-layer components needs computed laminography and VoidInspect.

Extended BGA inspection

Cougar allows to quickly select and index individual balls, either manually or using automatic grid detection. A wizard guides the operator through the workflow step-by-step and ensures perfectly accurate and repeatable results.

Automated sequences

The productivity of working with the Cheetah EVO on recurring test tasks can be significantly increased by automating and customizing test sequences via the scripting interface.

eHDR

To ensure highest product quality, the eHDR filter highlights complex structures with just one click. Thanks to our advanced software and enhanced 16-bit gray scale values, it detects even the slightest variances in gray scale, so that no defect will be missed. This allows operators to easily see faults that were invisible before.

Artifact reduction

Powerful image quality optimizations help improve the quality of the scan data, e.g. through BHR/BHC Beam Hardening Reduction/Correction, Ring Artifact Reduction or Noise Reduction.

Dose Monitoring

The Cougar's Dose Monitoring technology prevents damaging X-ray sensitive electronics during the inspection process. The absorbed X-ray dose is automatically monitored - when a critical threshold is reached, the operator is informed and the scan is aborted.

COMET YXLON COUGAR EVO

Life Cycle Service: supporting you every step of the way.

At Comet Yxlon, service is not an add-on, but an integral part of every product. We support you through the entire life cycle of your system – for easy operation and extended product life.

Offline applications, at-line scenarios, or in-line implementation – Comet Yxlon supplies tailored service solutions for a wide range of production environments. Whether you are an X-ray beginner or a CT expert, whether you need introductory training or a performance upgrade: Our service team is here to support you.

1. Getting you started

Our professional Comet Yxlon field service technicians or certified service providers will ease your way into working with your new inspection system.

- Bringing the system to life: installation & commissioning
- · Power on: introductory training by Comet Yxlon Academy
- Correct measurements from the start: SmartCalibration
- Cost transparency from the beginning: flat fee service rates

2. Running things smoothly

Is there an issue? No problem. Our skilled service technician team helps with troubleshooting, maintenance, and part exchange for easy operation.

- High efficiency thanks to remote control and VisualAssist
- Professional phone support and on-site visits
- Preventive maintenance and SmartExchange
- · High-end system monitoring with SmartCalibration

3. Enhancing performance

With our upgrades and conversion kits, your Comet Yxlon system remains in top-notch condition and keeps its value as market demands change.

- System release upgrades, feature & performance upgrades
- Component upgrades
- System software upgrades
- · Advanced Academy training

Tailor-made Service Level Agreements

Our Service Level Agreements are based on different performance factors, e.g.

ServicePass – for fast reaction times and seamless maintenance

SmartPass – focusing on the highest possible system availability

LifeCyclePass – the all-inclusive premium contract for guaranteed life-cycle-costs

Please contact us to learn more about the specifics of our different service contracts!

X-ray inspection system

Dimensions (w x d x h)	1,000 x 1,050 x 2,200 mm		
Weight	1,450 kg		
Mains connections	230 V ± 10% AC, 50/60 Hz, 1 Phase, neutral and ground conductor		
Fuse protection	16 A		
Max. power consumption	2.5 kVA		
Max. dose rate*	< 1µSv/h		
* at 100 mm distance to the cabinet surface			

Inspection parts

Max. part size	440 mm x 550 mm (17" x 21")
Max. radiographic area	310 mm x 310 mm (12" x 12")
Max. part weight (standard)	5 kg
Max. part weight rotation and tilt	2 kg

Manipulation

Manipulation control	via mouse or joystick
Manipulation axes	X, Y, Z(D)*
Oblique viewing	+/-70° (140°)

^{*} Manipulation options for horizontal and vertical rotation and tiltina available

General Product Features

Time to first image (typ.)	time (typ.) < 60 s ~ 3.15 min ions ime ~ 1.55 min		
Reconfiguration time (typ.)			
Acquisition time (Quick Scan) for 2000 projections			
Reconstruction time (Quick Scan) for 2000 projections			
Acquisition time (micro3Dslice Semicon) for 120 projections	~ 1.45 min		
Reconstruction time (micro3Dslice Semicon) for 120 projections	~ 0.30 min		
Access for sample loading	manual		
Cabinet window	380 mm x 200 mm		
Monitor	27" Ultrasharp, wide viewing angles		
Zoom+	yes		
PowerDrive	yes		

X-ray source	FXT-160.50 Microfocus	FXT-160.51 Multifocus	
Target	transmiss	sion	
Voltage range	20 – 160 kV		
Current range	0.001 – 1.0 mA		
Tube power	max. 64 W		
Target power	max. 15 W		
Target material	Tungste	en	
Detail detectability	0.75 μm	< 0.3 µm	
X-ray intensity control	TXI		
Optional	Dose Reduction Kit with collimator and filters for sensitive test parts		

Image Chain

Geometric magnification		~ 2,000 x
Total magnification	~	384,000 x
Spatial Resolution	1.5 µm	0.6 µm

Flat-panel detector	1308	1313	1515	1616
Max. resolution Pixel	1004 x 620	1004 x 1004	1280 x 1280	1276 x 1276
Pixel size	127 µm	127 µm	119 µm	127 µm
Pixel Area	128 mm x 79 mm	128 mm x 128 mm	152 mm x 152 mm	162 mm x 162 mm
A/D transformer	16 bit			

Please note that not all components and features described in this brochure belong to the standard configurations but are part of an optional selection.

Worldwide offices.

Germany - Headquarters

Comet Yxlon GmbH
Essener Bogen 15
22419 Hamburg
Germany
T. +49 40 527 290
E-mail: yxlon@comet.tech
https://yxlon.comet.tech

USA

Comet Technologies USA, Inc. 100 Trap Falls Road Ext Shelton, CT 06484 USA

T. +1 234 284 7849 E-mail: yxlon.us@comet.tech

Comet Mechanical Equipment

China

(Shanghai) Co., Ltd
Block B, 1F No.2, Lane 777
West Guangzhong Road,
Jingan District
200072 Shanghai, PRC
China
T. +86 21 38720918/992
E-mail: yxlon.cn@comet.tech

Japan

Comet Technologies Japan KK New Stage Yokohama Bldg. 1st Floor 1-1-32 Shinurashima-cho Kanagawa-ku 221-0031 Yokohama Japan T. +81 45 450 1730 E-mail: yxlon.jp@comet.tech

Taiwan

Comet Technologies Taiwan Ltd.
1st Floor, No. 120, Guangming Rd.
Qionglin Township
Hsinchu County 307001
Taiwan
T. +886 35922398
E-mail: yxlon.tw@comet.tech

Comet Yxlon GmbH reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

PB.CHE.EN.23/01.V01

